


## LifeScape Macro

UNIQUE DESIGN FOR THE NEEDS OF THE MODERN WORLD  
BEST FOR DISTANCE, COMPUTER INTERMEDIATE, & NEAR VISION

LifeScape Macro is at the forefront of progressive design philosophy by optimizing width in the areas most essential to daily use. While increasing the rate of change from distance to intermediate, its layout provides wide visual fields along with a soft, comfortable transition from the distance to the reading zone. This allows the wearer to quickly change from one zone to another, making everything in the modern world immediately accessible.

This lens was designed specifically for progressive wearers ages 40 and over who are experienced with or new to progressives and spend the majority of their time using electronic devices.




## LifeScape PAL


PERSONALIZED FOR YOUR NEEDS

The LifeScape PAL incorporates all of the latest design algorithms. It is fully Position-Of-Wear Compensated and uses Global Design Technology to create a truly advanced design.


What makes it unique is that the subtle shape of the corridor can be adjusted for a patient's preferences. This is accomplished simply by ranking in order of importance Distance, Intermediate and Near.




**1-3-2**  
BEST FOR DISTANCE  
& NEAR VISION



**1-2-3**  
BEST FOR DISTANCE &  
INTERMEDIATE VISION



**2-3-1**  
BEST FOR NEAR VISION



## OfficeSpace

### INDOOR DESIGN WITH ALL THE FLEXIBILITY YOU NEED

OfficeSpace is an occupational lens that offers comfortable near and intermediate focus with minimal lateral astigmatism and customizable focal lengths.

Available In 3 Vision Ranges:

- OfficeSpace 4ft  
(Clear vision up to 4ft)
- OfficeSpace 6ft  
(Clear vision up to 6ft)
- OfficeSpace 12ft  
(Clear vision up to 12ft)



## SerenityNOW

### INNOVATIVE DESIGN THAT REDUCES VISUAL FATIGUE

SerenityNOW is an anti-fatigue design calculated to reduce visual fatigue produced by a continuous changes in accommodation. SerenityNOW reduces the strain on muscles by providing the wearer with a small touch of addition in the bottom part of the lens. It is available in both 0.50D and 0.75D versions.



## LifeScape SV

### INCOMPARABLE EDGE-TO-EDGE VISION CLARITY

Freeform lenses can be used with single vision wearers to minimize distortion in every direction. The wearer's prescription is digitally mapped to all areas of the lens incorporating full position-of-wear compensation. The end result provides optimal visual comfort, especially for large prescriptions or astigmatisms.

